

For handle projection add 2 $\frac{1}{2}$ " to body depth. Dimensions of cladded safe are approximate.

Catalog No.	Code No.	DIMENSIONS						Clear Door Open.	Locking Lugs	Inner Door Open.	Inner Comp. Depth	Outer Comp. Depth	Est. Ship. Wt.
		Inside (Clear)			Outside (Body)								
		High	Wide	Deep	High	Wide	Deep						
209—TL-30	363040	14	14	12 $\frac{1}{2}$	16	16	17	9	4				520
With Inner Door	363060	14	14		16	16	17	9	4	5 $\frac{1}{2}$	*8 $\frac{1}{2}$	3 $\frac{1}{2}$	550
Unit in CB-3	363048	14	14	12 $\frac{1}{2}$	32	26	21	9	4				1720
In CB-3 with I/D	363058	14	14		32	26	21	9	4	5 $\frac{1}{2}$	*8 $\frac{1}{2}$	3 $\frac{1}{2}$	1750

*Allow 1 $\frac{1}{2}$ " for lock projection into inner compartment.

For handle projection add 4 $\frac{1}{2}$ " to body depth. (2 $\frac{1}{2}$ " with geared handle removed) Dimensions of cladded safe are approximate.

Catalog No.	Code No.	DIMENSIONS						Clear Door Open.	Locking Lugs	Inner Door Open.	Inner Comp. Depth	Outer Comp. Depth	Est. Ship. Wt.
		Inside (Clear)			Outside (Body)								
		High	Wide	Deep	High	Wide	Deep						
818—TL-30	363120	23	23	19 $\frac{1}{2}$	25	25	23 $\frac{1}{2}$	18	6				1300
With Inner Door	363130	23	23		25	25	23 $\frac{1}{2}$	18	6	8 $\frac{1}{2}$	*14 $\frac{1}{2}$	4 $\frac{1}{2}$	1385
Unit in CB-4	363124	23	23	19 $\frac{1}{2}$	32	32	28	18	6				2550
In CB-4 with I/D	363134	23	23		32	32	28	18	6	8 $\frac{1}{2}$	*14 $\frac{1}{2}$	4 $\frac{1}{2}$	2615

*Allow 1 $\frac{1}{2}$ " for lock projection into inner compartment.

For handle projection add 4 $\frac{1}{2}$ " to body depth. (2 $\frac{1}{2}$ " with geared handle removed) Dimensions of cladded safe are approximate.

Catalog No.	Code No.	DIMENSIONS						Clear Door Open.	Locking Lugs	Inner Door Open.	Inner Comp. Depth	Outer Comp. Depth	Est. Ship. Wt.
		Inside (Clear)			Outside (Body)								
		High	Wide	Deep	High	Wide	Deep						
718—TL-30	363160	30	28	20 $\frac{1}{2}$	32	30	25	18	6				1720
With Inner Door	363170	30	28		32	30	25	18	6	8 $\frac{1}{2}$	*15 $\frac{1}{2}$	4 $\frac{1}{2}$	1805
Unit in CB-5	363165	30	28	20 $\frac{1}{2}$	42	42	28	18	6				3900
In CB-5 with I/D	363175	30	28		42	42	28	18	6	8 $\frac{1}{2}$	*15 $\frac{1}{2}$	4 $\frac{1}{2}$	4365

*Allow 1 $\frac{1}{2}$ " for lock projection into inner compartment.